

GUBI CHAIR COLLECTION

GUBI 5 CHAIR UNUPHOLSTERED // 4-LEGS WOODEN BASE, NON STACKABLE

Designed by Komplot Design



The GUBI Chair Collection is a chair series in laminated moulded 3-D veneer or in the injection moulded HiRek material. The shell is 5 mm thick. Both types of the shells can be delivered upholstered, with front upholstered or fully upholstered in fabric or leather. The base is available in steel, in different finishes as specified below and moulded wood in various finishes. Several of the chair versions are stackable. The GUBI Chair series includes a side chair with and without arms, a bar stool, a lounge chair and a table series in 3 different heights.

VERSION - HIREK (PP PLASTIC MATERIAL)

RAL codes are indicative.

- Black // RAL 9005, silkmatt /
- Venetian Gold // RAL 080 7050 , silkmatt /
- Mistletoe Green // RAL 130 5010, silkmatt /
- Nightfall Blue // RAL 200 7005, silkmatt /
- Rainy Gray // RAL 7031, silkmatt /
- White Cloud // RAL 9001, silkmatt /
- Moon Gray // RAL 085 7010, silkmatt /
- Shy Cherry // RAL 3011, silkmatt /
- Oak base // Gloss 20-30
- Walnut base // Gloss 20-30
- Blackstained beech base // Gloss 20-30

CHAIR VERSION

Order item - look for part number in the pricelist.

The series consists of the following:

GUBI 5, GUBI 52, GUBI 53



MEASUREMENT - *L X W X H MM* Sitting height: 450 mm Seat width: 493 mm Seat depth: 544 mm

Seat height: 483 mm Back height: 373 mm Frame width: 519 mm Frame depth: 479 mm Chair height: 808 mm Shell thickness: 5 mm Legs width: 20 - 45 mm

WEIGHT ITEM 4,680 kg

PACKAGING TYPE Cardboard box

PACKAGING MEASUREMENT - *L X W X H CM* L:59 X W:55 X H:84 CM

WEIGHT PACKAGING - MATERIAL TYPE

- Delivery note: 5 g
- Cardboard box, FEFCO quality EB85BB: 2192 g
- Cardboard extra bottom: 408 g
- Polybag PE: 200 g - LD-EPE foam protector: 100 g
- Strapping: 10 g

WEIGHT PACKAGING - *TOTAL* 7,595 kg

NUMBER OF PARCELS 1 pcs.

- Defective frame and shells can be replaced.

GUBI[®]

GUBI 52 CHAIR FRONT UPHOLSTERED // 4-LEGS WOODEN BASE, NON STACKABLE

Designed by Komplot Design

PRODUCT



COLOURS



GUBI CHAIR COLLECTION

Item no.: 21001-52-XX + style code

$/// \setminus /// \setminus /// \setminus$

DESCRIPTION

The GUBI Chair Collection is a chair series in laminated moulded 3-D veneer or in the injection moulded HiRek material. The shell is 5 mm thick. Both types of the shells can be delivered upholstered, with front upholstered or fully upholstered in fabric or leather. The base is available in steel, in different finishes as specified below and moulded wood in various finishes. Several of the chair versions are stackable. The GUBI Chair series includes a side chair with and without arms, a bar stool, a lounge chair and a table series in 3 different heights.

VERSION - HIREK (PP PLASTIC MATERIAL) - FRONT UPHOLSTERED

RAL codes are indicative.

- Black // RAL 9005, silkmatt /
- Venetian Gold // RAL 080 7050 , silkmatt /
- Mistletoe Green // RAL 130 5010, silkmatt /
- Nightfall Blue // RAL 200 7005, silkmatt /
- Rainy Gray // RAL 7031, silkmatt /
- White Cloud // RAL 9001, silkmatt /
- Moon Gray // RAL 085 7010, silkmatt /
- Shy Cherry // RAL 3011, silkmatt /
- Oak base // Gloss 20-30
- Walnut base // Gloss 20-30
- Blackstained beech base // Gloss 20-30

CHAIR VERSION

Order item - look for part number in the pricelist.

The series consists of the following:

GUBI 5, GUBI 52, GUBI 53



MEASUREMENT - *L X W X H MM* Sitting height: 460 mm Seat width: 509 mm Seat depth: 550 mm Seat height: 493 mm Back height: 493 mm Frame width: 519 mm Frame depth: 479 mm Chair height: 816 mm Shell thcikness: 5 mm

FACTS

Front uphlestered: 10 mm Legs width: 20 - 45 mm WEIGHT ITEM

4,880 kg

PACKAGING TYPE Cardboard box

PACKAGING MEASUREMENT - *L X W X H CM* L:59 X W:55 X H:84 CM

WEIGHT PACKAGING - MATERIAL TYPE

- Delivery note: 5 g
 Cardboard box, FEFCO quality EB85BB: 2192 g
- Cardboard extra bottom: 408 g
- Polybag PE: 200 g
- LD-EPE foam protector: 100 g
- Strapping: 10 g

WEIGHT PACKAGING - *TOTAL* 7,792 kg


NUMBER OF PARCELS 1 p

GUBI[®]

ACCESSORIES

BLACK PLASTIC GLIDES FOR CARPETING ARE STANDARD. FELT GLIDERS ON REQUEST.

CHAIR SUSPENSION FOR TABLES.



CLEANING AND MAINTENANCE

For dusting and light cleaning of **the plastic surface** and frame use a soft, dry cloth. For further cleaning, use a soft cloth that is firmly wrung in clean water for gently wiping the surface, and then immediately use a dry cloth to wipe the surface again. If more thorough cleaning is necessary, use a mild detergent or washing-up liquid dissolved in water on a firmly wrung cloth. Afterwards, repeat the process with clean water as described above. Polish with a soft cloth after wiping.

Do not use materials for maintenance that:

Contain abrasive agents.

• Are basic, acidiferous or organic.

For the best maintenance of the product, protect it against sunlight and heat, and try to keep it away from moisture, grease and other dirt.

Furthermore, protect the surfaces against sharp objects and other that might scratch.

For dusting and light cleaning of **the wooden surface** and frame use a soft, dry cloth. For further cleaning, use a soft cloth that is firmly wrung in clean water for gently wiping the surface, and then immediately use a dry cloth to wipe the surface again. If more thorough cleaning is necessary, use a mild detergent or washing-up liquid dissolved in water on a firmly wrung cloth. Afterwards, repeat the process with clean water as described above. Polish with a soft cloth after wiping. Do not use materials for maintenance that:

Contain abrasive agents.

Are basic, acidiferous or organic.

For the best maintenance of the product, protect it against sunlight and heat, and try to keep it away from moisture, grease and other dirt. Furthermore, protect the surfaces against sharp objects and other that might scratch.

ENVIRONMENT

Parts can be separated and sorted for recycling.

Disposal of plastic type PP may be done with incineration of waste.

TESTS

EN 15373:2007 Furniture - Strength, durability and safety - Requirements for non-domestic seating. Loading according to Test severity 3. Severe use